


Terminal blocks spring clamp

Three level

DIN 3



End stop		th. 9 mm	BADL	V0	1SNA 399 903 R0200
End stop		th. 10 mm	BAM2 V0	V0	1SNA 399 967 R0100
End stop		th. 12 mm	BADH	V2	1SNA 116 900 R2700
End stop		th. 9,1 mm	BAMH	V2	1SNA 114 836 R0000
End stop		th. 9,1 mm	BAMH V0	V0	1SNA 194 836 R0100
Rail		35 x 7,5 x 1	PR3.22		1SNA 174 300 R1700
Rail		35 x 15 x 2,3	PR4		1SNA 168 500 R1200
Rail		35 x 15 x 1,5	PR5		1SNA 168 700 R2200


Other end stops, rails and accessories : see section on accessories.

Notes

UL 94 V0 material.
One wire per spring.


D 2,5/5.T3.L

Spacing 5 mm +0,05 .198"



D 2,5/5.T1.L

Spacing 5 mm +0,05 .198"




Colour	Type	Part number
Grey	D 2,5/5.T3.L	1SNA 290 456 R0000

Colour	Type	Part number
Black	D 2,5/5.T1.L	1SNA 290 457 R0100

Characteristics			
Wire size	IEC		UL/CSA
	NFC	DIN	
Rigid	0,14-4 mm ²		
Flexible	0,14-2,5 mm ²		
Isolating cover			2,5 mm ²
Ground bar			
Voltage			
Rated		500 V	
Impulse withstand		6 kV	
Pollution degree		3	
Current			
Rated		20 A	
Wire size			
Rated / Gauge		2,5 mm ² / A2	
Wire strip. length	Recomm. screwdriver	Weight	Protection
9,5 mm	3,5 mm		IP 20
.37"	.14"		NEMA 1

Characteristics			
Wire size	IEC		UL/CSA
	NFC	DIN	
Rigid	0,14-4 mm ²		
Flexible	0,14-2,5 mm ²		
Isolating cover			2,5 mm ²
Ground bar			
Voltage			
Rated		500 V	
Impulse withstand		6 kV	
Pollution degree		3	
Current			
Rated		24 A	
Wire size			
Rated / Gauge		2,5 mm ² / A2	
Wire strip. length	Recomm. screwdriver	Weight	Protection
9,5 mm	3,5 mm		IP 20
.37"	.14"		NEMA 1

Accessories



- 1 End section grey
- 2 Test plug black
- 3 Jumper bar orange
IP 20 - 24 A

Type	Part numbers
FED5.T3.L V0 th. 2,5 mm	1SNA 291 817 R1700
FC2.MC (1) V2 DIA 2,0 mm	1SNA 107 239 R0300
BJDL5.2 V0 2 poles	1SNA 291 102 R2300
BJDL5.3 V0 3 poles	1SNA 291 103 R2400
BJDL5.4 V0 4 poles	1SNA 291 104 R2500
BJDL5.5 V0 5 poles	1SNA 291 105 R2600
BJDL5.6 V0 6 poles	1SNA 291 106 R2700
BJDL5.7 V0 7 poles	1SNA 291 107 R2000
BJDL5.8 V0 8 poles	1SNA 291 108 R0100
BJDL5.9 V0 9 poles	1SNA 291 109 R0200
BJDL5.10 V0 10 poles	1SNA 291 110 R2600

Type	Part numbers
FED5.T3.L V0 th. 2,5 mm	1SNA 291 817 R1700
FC2.MC (1) V2 DIA 2,0 mm	1SNA 107 239 R0300
BJDL5.2 V0 2 poles	1SNA 291 102 R2300
BJDL5.3 V0 3 poles	1SNA 291 103 R2400
BJDL5.4 V0 4 poles	1SNA 291 104 R2500
BJDL5.5 V0 5 poles	1SNA 291 105 R2600
BJDL5.6 V0 6 poles	1SNA 291 106 R2700
BJDL5.7 V0 7 poles	1SNA 291 107 R2000
BJDL5.8 V0 8 poles	1SNA 291 108 R0100
BJDL5.9 V0 9 poles	1SNA 291 109 R0200
BJDL5.10 V0 10 poles	1SNA 291 110 R2600



R See section on markers marking method

On top : RC510 or RPC
On sides : RC55

On top : RC510 or RPC
On sides : RC55

(1) The use of the test plug decreases the block's voltage rating: U = 200 V.