

Coupling Size	Max Bore (in)		HP/100	Torque (in.-lbs)	Max RPM		Axial Misalignment (in.)	Angular Misalignment (degrees)	Coupling Size	Max Bore (mm)		KW/100	Torque (Nm)	Max RPM		Axial Misalignment (mm)	Angular Misalignment (degrees)
	Standard Hub	Large Hub			Standard	Balanced				Standard Hub	Large Hub			Standard	Balanced		
Dodge Disc Coupling									Dodge Disc Coupling								
94	1.680	2.250	3.3	2100	9100	22700	0.059	1.5	94	42.7	57.2	2.5	237	9100	22700	1.5	1.5
115	2.060	2.940	8.1	5100	7200	18000	0.083	1.5	115	52.3	74.7	6.0	576	7200	18000	2.1	1.5
139	2.690	3.560	15.4	9700	5840	14600	0.102	1.5	139	68.3	90.4	11.5	1096	5840	14600	2.6	1.5
165	3.130	4.130	28.1	17700	4920	12300	0.122	1.5	165	79.5	104.9	20.9	2000	4920	12300	3.1	1.5
193	3.750	4.940	46.3	29200	4200	10500	0.146	1.5	193	95.3	125.5	34.5	3299	4200	10500	3.7	1.5
210	4.060	5.380	64.6	40700	3840	9600	0.150	1.0	210	103.1	136.7	48.2	4598	3840	9600	3.8	1.0
236	4.500	5.940	98.4	62000	3400	8500	0.165	1.0	236	114.3	150.9	73.4	7005	3400	8500	4.2	1.0
263	4.940	6.630	143.3	90300	3080	7700	0.185	1.0	263	125.5	168.4	106.8	10202	3080	7700	4.7	1.0
286	5.500	7.310	199.4	125700	2800	7000	0.205	1.0	286	139.7	185.7	148.7	14202	2800	7000	5.2	1.0
310	6.130	7.880	280.8	177000	2560	6400	0.224	1.0	310	155.7	200.2	209.4	19998	2560	6400	5.7	1.0
Made-To-Order	12.630	15.250	3636.7	2292000	1360	3400	0.299	0.5	Made-To-Order	320.0	385.0	2711.6	258959	1360	3400	7.6	0.5
Rexnord Thomas									Rexnord Thomas								
150	1.500	2.375	1.5	930	9000	20800	0.050	0.5	150	38.1	60.3	1.1	105	9000	20800	1.3	0.5
175	1.875	2.750	2.6	1630	8300	17000	0.070	0.5	175	47.6	69.9	1.9	184	8300	17000	1.8	0.5
225	2.250	3.250	4.8	3060	7700	16000	0.075	0.5	225	57.2	82.6	3.6	346	7700	16000	1.9	0.5
300	3.000	4.000	11.5	7260	6800	14000	0.085	0.5	300	76.2	101.6	8.6	820	6800	14000	2.2	0.5
350	3.500	4.500	21.2	13400	6200	13500	0.090	0.5	350	88.9	114.3	15.9	1514	6200	13500	2.3	0.5
375	3.750	5.000	30.6	19300	5650	12000	0.950	0.5	375	95.3	127.0	22.8	2181	5650	12000	24.1	0.5
412	4.125	5.310	35.7	22500	5350	11000	0.110	0.5	412	104.8	134.9	26.6	2542	5350	11000	2.8	0.5
462	4.625	6.000	64.1	40400	5000	10000	0.120	0.5	462	117.5	152.4	47.8	4565	5000	10000	3.0	0.5
512	5.125	6.690	87.3	55000	4700	9200	0.130	0.5	512	130.2	169.9	65.1	6214	4700	9200	3.3	0.5
562	5.625	7.310	133.0	84100	4350	8300	0.145	0.5	562	142.9	185.7	99.5	9502	4350	8300	3.7	0.5
600	6.000	7.810	145.0	91700	4150	7800	0.160	0.5	600	152.4	198.4	108.5	10361	4150	7800	4.1	0.5
712	7.125	9.250	174.0	110000	3450	7200	0.082	0.5	712	181.0	235.0	130.1	12428	3450	7200	2.1	0.5
800	8.000	10.375	255.0	161000	3250	6800	0.092	0.5	800	203.2	263.5	190.5	18190	3250	6800	2.3	0.5
875	8.750	11.375	373.0	235000	3050	6400	0.102	0.5	875	222.3	288.9	278.0	26551	3050	6400	2.6	0.5
1038	10.375	13.125	549.0	346000	2900	5800	0.115	0.5	1038	263.5	333.4	409.3	39092	2900	5800	2.9	0.5
KOP-FLEX KD2 - Medium Duty									KOP-FLEX KD2 - Medium Duty								
23	1.500	2.000	2.3	1450	25500	Not published	0.040	Not published	23	38.1	50.8	1.7	164	25500	Not published	1.0	Not published
103	1.880	2.750	4.3	2710	17000	Not published	0.060	Not published	103	47.8	69.9	3.2	306	17000	Not published	1.5	Not published
153	2.880	4.000	12.5	7880	14200	Not published	0.075	Not published	153	73.2	101.6	9.3	890	14200	Not published	1.9	Not published
203	3.250	4.620	22.9	14400	12800	Not published	0.090	Not published	203	82.6	117.3	17.0	1627	12800	Not published	2.3	Not published
253	4.000	5.620	37.5	23600	11500	Not published	0.105	Not published	253	101.6	142.7	27.9	2666	11500	Not published	2.7	Not published
303	4.750	6.500	60.0	37800	10000	Not published	0.125	Not published	303	120.7	165.1	44.7	4271	10000	Not published	3.2	Not published
353	5.500	7.620	100.0	63000	8500	Not published	0.150	Not published	353	139.7	193.5	74.5	7118	8500	Not published	3.8	Not published
403	6.250	8.750	155.0	97700	7500	Not published	0.175	Not published	403	158.8	222.3	115.6	11039	7500	Not published	4.4	Not published
453	7.250	9.380	205.0	129000	7000	Not published	0.200	Not published	453	184.2	238.3	152.6	14575	7000	Not published	5.1	Not published
KOP-FLEX KD2 - Heavy Duty									KOP-FLEX KD2 - Heavy Duty								
204	3.250	4.620	57.1	36000	13000	Not published	0.110	Not published	204	82.6	117.3	42.6	4067	13000	Not published	2.8	Not published
254	4.000	5.620	82.5	52000	11200	Not published	0.140	Not published	254	101.6	142.7	61.5	5875	11200	Not published	3.6	Not published
304	4.750	6.500	141.0	89000	9900	Not published	0.170	Not published	304	120.7	165.1	105.3	10056	9900	Not published	4.3	Not published
354	5.500	7.620	238.0	150000	8800	Not published	0.200	Not published	354	139.7	193.5	177.5	16948	8800	Not published	5.1	Not published
404	6.250	8.750	340.0	215000	7800	Not published	0.225	Not published	404	158.8	222.3	254.4	24292	7800	Not published	5.7	Not published
454	7.250	9.380	405.0	255000	7200	Not published	0.250	Not published	454	184.2	238.3	301.7	28811	7200	Not published	6.4	Not published
504	7.500		570.0	360000	6600	Not published	0.275	Not published	504	190.5		425.9	40674	6600	Not published	7.0	Not published
554	8.250		800.0	505000	6100	Not published	0.300	Not published	554	209.6		597.5	57057	6100	Not published	7.6	Not published
604	9.000		1050.0	660000	5600	Not published	0.320	Not published	604	228.6		780.8	74569	5600	Not published	8.1	Not published
705	10.880		2400.0	1510000	4500	Not published	0.270	Not published	705	276.4		1786.4	170606	4500	Not published	6.9	Not published
805	12.250		3670.0	2310000	4000	Not published	0.310	Not published	805	311.2		2732.9	260993	4000	Not published	7.9	Not published
905	13.500		4130.0	2600000	3600	Not published	0.400	Not published	905	342.9		3076.0	293758	3600	Not published	10.2	Not published

