

ABB industrial drives  
ACS880-01, single drives, 0.55 to 250 kW



The ACS880-01 is part of ABB's new all-compatible drives portfolio. The drives are compatible with virtually all types of AC motors, automation systems, users and business requirements.



The innovation behind all-compatibility is ABB's new common architecture, designed to simplify operation, optimize energy efficiency and maximize output.

**Simplifying your world without limiting your possibilities**

The ACS880-01 is a wall-mounted single drive compatible with a wide range of applications in a broad range of industries such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills and marine. At the heart of the drive is direct torque control (DTC), ABB's premier motor control technology. The extensive range of options include EMC filters, encoders, resolvers, du/dt filters, sine filters, chokes and brake resistors, remote monitoring tool, as well as application-specific software. Built-in safety features reduce the need for external safety components. Multiple drives can be daisy-chained for synchronized drive-to-drive communication. The drive offering includes two enclosure ratings, IP21 and IP55, for dusty and wet environments.

**Learn it once, use it everywhere**

The common drives architecture features the same control panel, parameter menu structure, universal accessories and engineering tools. The new control panel is equipped with an intuitive and high-resolution control display that enables easy navigation. Many flexible data visualizations including bar charts, histograms and trend graphs help users to analyze processes. The menus and messages are customizable for the specific terminology of different applications. An integrated USB port allows easy connection to the Drive composer PC tool, which offers fast and harmonized start-up, commissioning and monitoring. The built-in energy calculators, including used and saved kWh, CO<sub>2</sub> reduction and money saved, help the user fine-tune processes to ensure optimal energy use. The energy optimizer control mode ensures the maximum torque per ampere, reducing energy drawn from the supply.



3AUAA0000089906 REV F EN 7.3.2013 #16707

**Technical data**

<b>Voltage and power range</b>	3-phase, $U_{N2}$ = 208 to 240 V, +10/-15% 3-phase, $U_{N3}$ = 380 to 415 V, +10/-15% 3-phase, $U_{N5}$ = 380 to 500 V, +10/-15% 3-phase, $U_{N7}$ = 525 to 690 V, +10/-15% 0.55 to 250 kW
<b>Frequency</b>	50/60 Hz ±5%
<b>Mains choke</b>	Standard (built-in)
<b>Degree of protection</b>	IP21 (UL type 1) and IP55 (UL type 12)
<b>Ambient temperature</b>	-15 to +55 °C, (>40 °C with derating)
<b>Compliance</b>	CE, TÜV Nord (safety functions), UL, GOST R; pending: cUL, CSA, C-Tick
<b>Safety functions (TÜV Nord certified)</b>	Safe torque-off (STO), safe stop 1 (SS1), safely-limited speed (SLS), safe brake control (SBC) and safe maximum speed (SMS), safe stop emergency (SSE)
<b>EMC</b>	According to IEC 61800-3, class C3 and C2 as internal option
<b>Harmonic mitigation</b>	According to IEC 61000-3-12
<b>Control connections</b>	Two analog inputs, two analog outputs, six digital inputs including thermistor input, two digital inputs/outputs, three relay outputs, digital input interlock, drive-to-drive link (or Modbus RTU), safe torque-off (STO), external 24 V DC supply input, memory unit connection, USB via control panel

**Control and communication options**

<b>Fieldbus adapter modules</b>	PROFIBUS DP, DeviceNet™, CANopen®, EtherNet/IP™, Modbus TCP, PROFINET IO, EtherCAT®, Modbus RTU, PowerLink
<b>Optional I/O extension modules</b>	FIO-01: four digital inputs/outputs, two relay outputs FIO-11: three analog inputs, one analog output, two digital inputs/outputs FDCO-01, FDCO-02: DDCS communication options
<b>Feedback modules</b>	HTL pulse encoder, TTL pulse encoder, absolute encoder, resolver
<b>PC tools</b>	Drive composer entry Drive composer pro

For more information contact your local ABB representative or visit:

[www.abb.com/drives](http://www.abb.com/drives)  
[www.abb.com/drivespartners](http://www.abb.com/drivespartners)



© Copyright 2013 ABB. All rights reserved.  
Specifications subject to change without notice.